



ENVIRONMENTAL DECLARATION

Issued by Annika Hedebark

Date 2003-07-29

- 1 Product** **VÄRMEKABEL US 12 HF**
- 2 Supplier** **Nexans IKO Sweden AB**
S-514 81 GRIMSÅS
SWEDEN
Phone: +46 325 –800 00
Fax: +46 325 –803 20
www.nexans.se
Nexans IKO Sweden AB has a EMAS registration and is certified according to ISO 9001 and ISO 14001
- 3** Conductor: Tin-coated copper
Filler string: Polyethylene.
Semi-conductor: Polyethylene containing soot.
Insulation: Polyethylene
By-conductor: Tin-coated copper
Tape: Aluminium/polyethylene laminate
Sheath: Polyethylene.
- 4 Materials on the Swedish National Chemicals Inspectorate's Limitation list or Observation list** Copper
- 5 Packaging** The cable is delivered on one-way polystyrene plastic drum.
Nexans IKO Sweden AB is a member of the Swedish REPA association.
- 6 Recycle Reuse Scrap** Aluminium and copper metal can be reused. Polyethylene and polystyrene can be reused as plastic or as an energy source.
- 7 Other environmental aspects** The cable itself does not effect the environment under normal use.